

PRODUCT BULLETIN - PB-152.R2

ALS Built Design 6 Electric Heat Kit 240 VAC to 208 Voltage Conversion



Summary

To ensure product performance and longevity it is critical that all electric heated drying tumblers are connected to the correct voltage for their specific rated tumbler.

Connecting 240VAC rated electric tumbler to 208VAC utility will cause a reduction in kW heat output. This will result in slightly longer dry times. There are kits available for some models which allow you to field convert your tumblers heating elements from 240 VAC to 208 VAC

1 Brand	2 Market	3-5 Capacity	6 Heater	7 Control	8-9 Activation	10 Reversing	11 Voltage	12 Cylinder/ Moisture Sense	13 Design
K	T	075	E	F	NN0	R	G	H	6

Model	Voltage Conversion Kit Part Number to Convert from 240 VAC to 208VAC
KTT30 or GTT30	ALS44391001
KT030 or GT030	ALS44391002
KT055 or GT055	ALS44391003
KT075 or GT075	ALS44391004
KTS30	ALS44391002

*** Always follow the warnings and procedures in the corresponding equipment instruction manual.